

Selection and Ordering data	Article No.
The Probe Short-range integrated ultrasonic level transmitter, ideal for liquids and slurries in open or closed vessels  Click on the Article No. for the online configuration in the PIA Life Cycle Portal.	 7ML1201-00
Measuring range 5 m (16.40 ft)	 1
Transducer/Process connection PVDF copolymer, 2" NPT [(Taper), ANSI/ASME B1.20.1] PVDF copolymer, R 2" [(BSPT), EN 10226] PVDF copolymer, G 2" [(BSPP), EN ISO 228-1] PVDF copolymer, 4" Sanitary mounting	 E  F  G  J
Model/Approval 3 Wire, 24 V DC, CE, RCM, CSA, FM 2 Wire, 24 V DC, CE, RCM, CSA	 E  F

 We can offer shorter delivery times for configurations designated with the Quick Ship Symbol . For details see page 9/5 in the appendix.

Selection and Ordering data	Order code
Further designs Please add "-Z" to Article No. and specify Order code(s).	
Acrylic coated, stainless steel tag [13 x 45 mm (0.5 x 1.75 inch)]: Measuring-point number/identification (max. 20 characters) specify in plain text	 Y17
Additional Operating Instructions 3 Wire, 24 V model, Multi-language manual 2 Wire model, Multi-language manual	Article No. 7ML1998-5GD62 A5E32243983
Accessories Universal Box Bracket Mounting kit Sanitary 4" mounting clamp 3" ASME, DN 65 PN 10, JIS 10K 3B ETFE Flange adapter for 2" NPT 3" ASME, DN 65 PN 10, JIS 10K 3B ETFE Flange adapter for 2" BSPT 2" NPT locknut, plastic 2" BSPT locknut, plastic Plastic M20 cable gland with metal locknut SITRANS RD100, loop powered display - see Chapter 7 SITRANS RD200, universal input display with Modbus conversion - see Chapter 7 SITRANS RD300, dual line display with totalizer and linearization curve and Modbus conversion - see Chapter 7 SITRANS RD500 web, universal remote monitoring solution for instrumentation - see Chapter 7 For applicable back up point level switch see point level measurement section.	7ML1830-1BK 7ML1830-1BR 7ML1830-1BT 7ML1830-1BU 7ML1830-1DT 7ML1830-1DQ 7ML1930-1DB 7ML5741-... 7ML5740-... 7ML5744-... 7ML5750-...

 We can offer shorter delivery times for configurations designated with the Quick Ship Symbol . For details see page 9/5 in the appendix.